

Hydraulic Technologies
 5885 11th Street
 Rockford, IL 61109-3699 USA

Tech. Services: (800) 477-8326
 Fax: (800) 765-8326
 Order Entry: (800) 541-1418
 Fax: (800) 288-7031

Internet Address:
<http://www.powerteam.com>

Parts List for:

100951
 100952
 100953

 SINGLE-ACTING, CARTRIDGE STYLE MOUNT
 SWING / PULL CLAMP

Capacity: 750 lbs. Clamping Force (with 1.25" lg. arm) at 5,000 PSI (350 Bar) Max.

- 100951 - Left Hand, .345" Stroke
- 100952 - Right Hand, .345" Stroke
- 100953 - Straight Pull, .345" Stroke


The piston rod U-cup seal (Item 12) can be easily twisted if installed incorrectly.

Before installing the piston rod (Item 14) lubricate the rod and all seals with hydraulic oil. Install the rod with light pressure and a twisting motion as the seal is first contacted.

Refer to any operating instructions included with this product for detailed information about operation, testing, disassembly, reassembly, and preventive maintenance.

Items found in this parts list have been carefully tested and selected. Therefore: Use only genuine Hytec replacement parts!

Additional questions can be directed to our Technical Services Department.



Parts List, Form No. 101661, Back sheet 1 of 1

Item No.	Part No.	No. Req'd	Description
1	251910	1	Cap Screw (1/4-20 UNC x 3/8 Lg.; Torque to 100/125 in. lbs.)
2	* 11495	1	O-ring (1-13/32 X 1-11/64 X .116)
3	* 16817	2	Backup Washer
4	* 16684	1	O-ring (1-3/16 X 1" X 3/32)
5	* 208721	3	Backup Washer (3/4 O.D. X 9/16 I.D. X 3/64)
6	* 251895	1	Special Washer (NOTE: Assemble washer (Item #6) with larger radii towards teflon washer (Item #5). Must be grease and oil free.)
7	351136	1	Rotating Cam (Left Hand† 90° for 100951)
	351137	1	Rotating Cam (Right Hand† 90° for 100952)
	351135	1	Rotating Cam (Straight Pull for 100953)
8	251909	1	Spring Pin
9	351152	1	End Cap (Torque to 35/45 ft. lbs.)
10	251897	1	Compression Spring (.730 O. D. x 2.660)
11	351140	1	Swing Clamp Body
12	* 216328	2	U-cup Packing
13	* 216289	1	Rod Wiper
14	351138	1	Piston Ass'y

Part numbers marked with an asterisk (*) are contained in Repair Kit No. 300869.

† Right hand rotation is clockwise rotation when viewed from the piston rod end.

Left hand is counterclockwise rotation. To reverse clamp rotation, order the appropriate rotating cam.

Note: Shaded areas reflect last revision(s) made to this form.